

Manuals:

Serial Highspeed Com-Servers

Type 58631, 58651, 58641, 58642, 58633, 58031, 58034, 58231, 58431, 58331, 58334

Current manuals:

Date	Changes and comments	Manual revision
02.12.2009	<ul style="list-style-type: none"> New IP assignment wizard WuTility Firmware Update section expanded 	2.16 PDF download

Short Manual

Date	Changes and comments	Manual revision
April 22, 2008	<ul style="list-style-type: none"> Short manual for all W&T network devices Hardware installation overview Network startup using WuTility 	3.0 PDF download

Older manuals:

Date	Changes and comments	Manual revision
July 14, 2009	<ul style="list-style-type: none"> Com-Server Highspeed PoE 20mA, 58642 added 	2.15 PDF download
May 4, 2009	<ul style="list-style-type: none"> Effective firmware revision 1.60 and higher Formula for baud rate divider corrected "COM Port Redirector" section updated 	2.14 PDF download
August 22, 2008	<ul style="list-style-type: none"> Effective firmware revision 1.60 and higher Configurable serial Receive Buffer added 	2.13 PDF download
May 20, 2008	<ul style="list-style-type: none"> Valid for firmware revision 1.58 and higher COM Port Redirector 3.00 added OPC communication added Com-Server Highspeed 100BaseFX 58651 added 	2.12 PDF download
July 19, 2007	<ul style="list-style-type: none"> Applicable from firmware revision 1.52 Wiring example for 20mA interface Processing the <i>Prot-Char</i> for ASCII-Transmission in FTP client mode 	2.11 PDF download
November 8, 2006	<ul style="list-style-type: none"> Applicable from firmware revision 1.52 DHCP added DNS added TCP port for ControlPort can be set Com-Server 58641/Power-over-Ethernet added 	2.10 PDF download
October 21, 2005	<ul style="list-style-type: none"> Effective as of firmware revision 1.46 58631/UL added Switching between network speeds and Duplex procedure 	2.09 PDF download
May 9, 2005	<ul style="list-style-type: none"> Effective as of firmware revision 1.45 Assigning all network parameters using WuTility included 	2.08 PDF download
November 9, 2004	Serial Highspeed Com-Server - Hardware, Firmware, Protocols <ul style="list-style-type: none"> Inserted technical data Com-Server Highspeed Isolated Declaration of Conformity updated Effective as of firmware revision 1.40 	2.07 PDF download

Date	Changes and comments	Manual revision
July 29, 2004	Serial Highspeed Com-Server - Hardware, Firmware, Protocols <ul style="list-style-type: none"> • Effective as of firmware revision 1.40 • Web Based Management and its activation documented • Com-Server Highspeed Isolated added • New example for paired use as SLIP router • IP assignment using WuTility documented 	2.06 PDF download
February 12, 2004	<ul style="list-style-type: none"> • Applicable from firmware revision 1.37 • Keep-alive check added • Serial assignment of subnet mask and gateway added 	2.05 PDF download
October 8, 2003	<ul style="list-style-type: none"> • Applicable from firmware revision 1.35 • 19" and compact model added • Factory defaults via jumpers 	2.04 PDF download
March 12, 2003	<ul style="list-style-type: none"> • Applicable from firmware revision 1.32 • Fixed IP routes documented • Send/receive of BREAK documented • Various typographical errors corrected 	2.03 PDF download
October 7, 2002	<ul style="list-style-type: none"> • OEM and Office models added • Control structure revised 	2.01 PDF download
August 14, 2002	<ul style="list-style-type: none"> • Applicable from firmware revision 1.26 	2.00 PDF download



We are available to you in person:

Wiesemann & Theis GmbH
 Porschestra. 12
 42279 Wuppertal
 Phone: +49 202/2680-110 (Mon.-Fri. 8 a.m. to 5 p.m.)
 Fax: +49 202/2680-265
 info@wut.de

© Wiesemann & Theis GmbH, subject to mistakes and changes: Since we can make mistakes, none of our statements should be applied without verification. Please let us know of any errors or misunderstandings you find so that we can become aware of and eliminate them.

[Data Privacy](#)