

Current manuals:

RS232 isolators 1kV, 4kV and 50kV**Types 88001, 88004 and 88050**

Date	Changes and comments	Manual revision
September 19, 2019	<ul style="list-style-type: none">Safety notices revised, new layout	1.40 PDF download
September 28, 2009	<ul style="list-style-type: none">Safety notices added	1.30 PDF download
February 14, 2007	RS232 isolator 88001 and 88050: <ul style="list-style-type: none">Note on the dependency of the lower baud rate limit on the output voltage of the connected interface added	1.20 PDF download
February 1, 2005	RS232 isolator 88001, 88004 and 88050, all device revisions <ul style="list-style-type: none">Adapter set for 9-pole interfaces added	1.10 PDF download



We are available to you in person:

Wiesemann & Theis GmbH
Porschestra. 12
42279 Wuppertal
Phone: +49 202/2680-110 (Mon.-Fri. 8 a.m. to 5 p.m.)
Fax: +49 202/2680-265
info@wut.de

© Wiesemann & Theis GmbH, subject to mistakes and changes: Since we can make mistakes, none of our statements should be applied without verification. Please let us know of any errors or misunderstandings you find so that we can become aware of and eliminate them.

[Data Privacy](#)